




Material材料

Insulator塑胶:30%Glass filled PBT, (UL 94V-0)

Contact 端子: Brass黄铜

Electrical Characteristics电气特性


Current rating额定电流:1.5AMP

Dielectric Withstanding Voltage耐压:
AC 1000V for 1Minute.

Insulator Resistance绝缘电阻:
1000M Ω Min. AT DC 500V.

Contact Resistance接触电阻:30M Ω Max. AT DC 100mA.

Operating Temperature工作温度:-40 $^{\circ}$ C~+105 $^{\circ}$ C



未注公差尺寸			KSM9001-11641C 364		上海洲日电子有限公司						
尺寸	公差				Shanghai Zhouri Electronics CO.,LTD						
	长度	角度			上海康司玛电子设备进出口有限公司						
	X.	±0.3			±5°	Shanghai KangSiMa Eletronic Equipment					
	X.X	±0.2			±3°	import and export Co.,LTD					
X.XX	±0.15		版本号	20171018 A/0							
绘图	周元金	201171018	图编号	ZR20171018-42	TEL:86-21-34975176/51571121						
审核	张海娜	201171018	物料编号	110661		1:1		mm	图幅	A4	
核准	章妹	20181113				: 1 1					