


Coaxial PCB Connector 91_SMP-50-0-S1/111_N

Description

Edge mount PCB plug

Interface Standards
MIL-STD-348 SMP



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	40 GHz

Mechanical Data

Board mounting type	edge mount
Weight	0.00061 kg

Environmental Data

Operating temperature	-55 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing	DOU-00316763
-----------------	--------------

Ordering Information

Single package	91_SMP-50-0-S1/111_NE
----------------	-----------------------