



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		D3	REVISED PER ECO-12-021425	11DEC12	KH	DR



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
26-22 AWG STRANDED	NOT LISTED	NOT LISTED



- 1

STAMP AMP APPROX AS SHOWN
- 2

0.00254 [.000100] MIN TIN PER ASTM B-545
- 3

CLEANED, UNPLATED
- 4

0.00254 [.000100] MIN EXT THK GOLD PL PER ASTM B-488 OVER 0.00076 [.000030] MIN NICKEL PER SAE AMS QQ-N-290.
- 5

COPPER PER ASTM B-152, ANNEALED
- 6

NOTE DELETED
- 7

0.0050[.000200] MIN EXT THK NICKEL PLATE PER SAE AMS QQ-N-290.

32859

1000	LOOSE PIECE	7	2-32859-4
		4	2-32859-5
		3	32859-1
		2	32859
QTY	PACKAGE TYPE	FINISH	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN TA BRINKMAN 2-2-93		 TE Connectivity									
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK DA PATTERSON 2-2-93		NAME TERMINAL, RING TONGUE, BUDGET -							
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 0.1-0.41mm ² [202-810] STRANDED				APVD JL MECKLEY 2-2-93		PRODUCT SPEC -					APPLICATION SPEC -				
TOOLING INFORMATION		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				MATERIAL 		FINISH SEE TABLE		WEIGHT -		SIZE A2		CAGE CODE 00779		DRAWING NO C-32859	
FOR ORDER ENTRY		1-800-526-5142								CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1		REV D3			