





FEMALE STRAIGHT RECEPTACLE FOR PCB

R128.426.700

SOLDER LEGS

Series : BMA-COM


PCB MOUNTING

SCALE : 1


All dimensions are in mm.

COMPONENTS	MATERIALS	PLATING (μm)
BODY	BRASS	NICKEL 2 GOLD 0.2
CENTER CONTACT	BERYLLIUM COPPER	NPGR
OUTER CONTACT	BERYLLIUM COPPER	NPGR
INSULATOR	PTFE	
GASKET	-	-
OTHERS PARTS	-	-
-	-	-
-	-	-

Issue : 0941 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL

FEMALE STRAIGHT RECEPTACLE FOR PCB**R128.426.700****SOLDER LEGS**Series : **BMA-COM****PACKAGING**

Standard	Unit	Other
100	'W' option	Contact us

SPECIFICATION**ELECTRICAL CHARACTERISTICS**

Impedance	50	Ω
Frequency	0-22	GHz
VSWR	1.25* + 0,0000	x F(GHz) Maxi
Insertion loss	0.07*	$\sqrt{F}(\text{GHz})$ dB Maxi
RF leakage	- (90*	- F(GHz)) dB Maxi
Voltage rating	350	Veff Maxi
Dielectric withstanding voltage	1000	Veff mini
Insulation resistance	5000	M Ω mini

ENVIRONMENTAL

Operating temperature	-65/+165	$^{\circ}\text{C}$
Hermetic seal	NA	Atm.cm3/s
Panel leakage	NA	

OTHER CHARACTERISTICS

Assembly instruction

Others :

*R.O.S 1.25 Maxi à 10 GHz

Coaxial transmission line only

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	18 N mini
Axial force – Opposite end	18 N mini
Torque	NA N.cm mini

Recommended torque

Mating	NA N.cm
Panel nut	NA N.cm

Mating life	1000 Cycles mini
Weight	1,8100 g

Issue : 0941 B

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 