

4

3

2


1

© - TE Connectivity. All Rights Reserved.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


SUGGESTED PCB LAYOUT



METAL PANEL



UNIT: mm / inch
TOLERANCES: ± 0.10 / 0.004
ONLY FOR THIS VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GAMESH C M 16AUG2016	 TE Connectivity Ltd.		
		CHK FRANZ MUELLER 16AUG2016			
		APVD MARTIN SZELAG 16AUG2016	NAME RJ45 JACK INT.MAG. 10/100 1x1 INV		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$			
MATERIAL 		FINISH 			
			PRODUCT SPEC 108-94552		
			APPLICATION SPEC 114-94447		
			WEIGHT	SIZE A3	CAGE CODE 00779
			CUSTOMER DRAWING	DRAWING NO C=2301994-3	RESTRICTED TO -
			SCALE 3:1	SHEET 2 of 3	REV B3

