

Coaxial Cable Connector 11_4310-50-12-Y60/033_-E

Description

Straight cable plug

Interface standards

IEC 61169-54

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	12 GHz
Frequency range	DC to 2.7 GHz
Return loss	32 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped

Environmental Data

Operating temperature	-55 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPALATE (R) Plating
Body	Brass	SUCOPALATE (R) Plating
Other body part	Brass	SUCOPALATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPALATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00341509
Assembly instruction	DOC-0000799919

Ordering Information

Single package	11_4310-50-12-Y60/033_-E
----------------	--------------------------

Additional Information

Suitable cables	SUCOFEE_1/2_PW, SUCOFEE_1/2, SUCOFEE_1/2_FR, SUCOFEE_1/2_LW
-----------------	---

Remarks

Other suitable cables: RFS CELLFLEX LCF-50JFN, ICA12-50JPLW, ICA12-50JPLLW, ICA12-50JPL, ANDREW/COMMSCOPE LDF4-50A / Assembly instructions: Foam-DOC-0000799919, Plenum-DOC-0000736630 / Note: Use blade unit 74_Z-0-12-21, 85068959 (colour green)