









NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: GOLD OVER SILVER
5. CONTACT RATING: 0.3A @ 125VAC
6. OPERATING FORCE: 800 $\pm$ 300 gf-cm
7. OPERATING TEMP: -30°C to 85°C
- ▲ 8. CIRCUIT SP: 12 POSITION NO STOPS.
9. DIELECTRIC STRENGTH: 500VAC FOR 1 MIN.
- ▲ 10. HARDWARE SUPPLIED ON SWITCH: LOCKWASHER, HEXNUT
11. ▲ DENOTES CRITICAL PARAMETER.



B	23845	correct pcb layout	4/9/19	MW
A	22232	RELEASED FOR PRODUCTION	4/11/16	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE KC10A7.001NPF

SCALE 1.5:1

DATE 4/11/2016

DR MJR

DWG G510613

REV B