

NOTES: UNLESS OTHERWISE SPECIFIED
1. FOR GENERAL SERIES SPECIFICATIONS, SEE SDPRF-206.

2. MATERIAL SPECIFICATIONS:
BAYONET SLEEVE, BODY: BRASS PER ASTM B16
INSULATOR: TEFLON PER ASTM D1710
CONTACT, SPRING WASHER, OUTER CONTACT: BERYLLIUM COPPER, ASTM B196
GASKET: SILICONE RUBBER, A-A-59588



3. FINISH SPECIFICATIONS:
BAYONET SLEEVE, BODY: .000100MIN NICKEL PER AMS-QQ-N-290
OVER COPPER FLASH PER ASTM B734 (ROHS)
CONTACT: .000030 MIN. GOLD PER ASTM B488, OVER .000080 MIN NICKEL PER AMS-QQ-N-290 (ROHS)

ALL OTHER METAL PARTS: .000050 MIN NICKEL PER AMS-QQ-N290 OVER
.000050 MIN COPPER PER ASTM B734 (ROHS)

4. ELECTRICAL SPECIFICATIONS:
IMPEDANCE: 75 OHMS
FREQUENCY RANGE: DC TO 12 GHz
RETURN LOSS: -25 dB @ 6 GHz

5. COMPLIANT TO 3G/6G/12G-SDI SMPTE REQUIREMENTS.

REV	DESCRIPTION	BY DATE	APPD
C	ER064328	91/17/17	VA



CATALOG P/N: 206H-034-00001N

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: XX [X.X] ± .01 [0.3] .XXX [X.XX] ± .005 [0.13] .XXXX [X.XXX] ± .XXXX ANGLES: ± 2° SCALE: 3:1				KINGS by WINCHESTER Winchester Electronics Corporation 62 Barnes Industrial Road North Wallingford, Connecticut 06492			
CUSTOMER SALES DRAWING				BNC MALE TO 1.0/2.3 FEMALE ADAPTOR(ROHS)			
DRAWN	DATE	APPROVED	DATE	A SD206H-034-00001N SHIT OF REV 1 1 C			
COL	08/08/11	DCBm	08/15/11				
APPROVED	DATE	APPROVED	DATE				
XXX	XX/XX/XX	XXX	XX/XX/XX				