






LOC		DIST		REVISIONS						
AD	00	P	LTR	DESCRIPTION			DATE	DWN	APVD	
			B	REVISED PER ECO-11-025276			04JAN12	KH	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 02DEC2010	TE Connectivity	
DIMENSIONS:		CHK J. EABY 02DEC2010		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 02DEC2010	NAME IMPACT, 2 PAIR, 10 COLUMN, HEADER	
	3 PLC ±.25	PRODUCT SPEC	LEFT GUIDED, OPEN END WALL	
	5 PLC ±0.13	APPLICATION SPEC	SIGNAL MODULE, 0.39 PTH	
MATERIAL	FINISH SEE TABLE	WEIGHT	SIZE CAGE CODE DRAWING NO	RESTRICTED TO
		CUSTOMER DRAWING	A100779C=2057419	-
			SCALE 6:1	SHEET 1 OF 2 REV B

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057419-6
	4.9	2057419-5
	4.5	2057419-4
	5.5	2057419-3
	4.9	2057419-2
	4.5	2057419-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 02DEC2010		 TE Connectivity	
CHK J. EABY 02DEC2010		APVD J. EABY 02DEC2010			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		9 PLC ±0.25 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.13 4 PLC ±0.13 ANGLES ±0.13		IMPACT, 2 PAIR, 10 COLUMN, HEADER LEFT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO	
-		SEE TABLE		A100779C=2057419	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 5:1 SHEET 2 OF 2 REV B	