


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECN-21-107697	30JUN2021	PZ	WKH



ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Impedance (Ohm): <u>50</u>	Interface Dimension <u>1.35mm male</u>	TEMPERATURE RANGE <u>-40 °C~+85 °C</u>
Frequency Range: <u>DC to 90GHz</u>	Force to Engage and Disengage Engage: <u>N/A</u> Disengage: <u>N/A</u>	ROHS <u>COMPLIANT</u>
Voltage Rating (Peak) @ Sea Level <u>150 V RMS</u>	Center Contact Captivation Axial (N) <u>26.0 MIN</u> Radial (In/Oz) <u>N/A</u>	
Insulation Resistance (MIN.) <u>5000 M ohms</u>	Cable Retention Axial (Lbs) <u>N/A</u>	
Contact Resistance (mohms MAX) Center Contact <u>4.0</u> Outer Contact <u>1.0</u>	Mating cycles <u>500 cycles</u>	
Dielectric Withstand Voltage: <u>500 V RMS Max</u>		
Insertion Loss : TBD		
VSWR: <u><1.50 @ DC ~ 90GHz</u>		

1	SHELL	STAINLESS STEEL	PASSIVATION
1	CONTACT PIN	BERYLLIUM COPPER	GOLD 50 u"/NICKEL /COPPER
1	INSULATOR	PEEK	N/A
1	BODY	STAINLESS STEEL	PASSIVATION
2385342-1	PART NUMBER	MATERIAL	PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PENG ZHAI 27JAN2021	 TE Connectivity				
		CHK ROGER SONG 27JAN2021					
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APVD WENKE HE 27JAN2021	NAME 1.35mm Male to 1.35mm Male Adapter —			
		0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.1 4 PLC ± — ANGLES ± 5°	PRODUCT SPEC —				
		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-2385342	RESTRICTED TO —	
MATERIAL —		FINISH —	WEIGHT —				
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 of 1	REV A		

2385342