




THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
(C) COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

- 1 MATERIAL:
CONTACT: PHOSPHOR BRONZE.
HOUSING: GLASS-FILLED POLYESTER.
- 2 GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1.27 μ m MIN NICKEL AND ACTION
PIN: 0.5 μ m MIN TIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- 3 CONFORMS TO ALL TESTING ACCORDING TO IEC 61076-4-101
PERFORMANCE LEVEL 2.
- 4 FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".
- 5 FOR ACTUAL PIN DIMENSIONS SEE "CONTACT DIMENSIONS".
- 6 TO BE MEASURED AT BOTTOM OF SHROUD.
- 7 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
ADDITIONAL CHARACTERS OR MARKINGS, AS WELL AS THE LOCATION OF THE MARKINGS,
MAY BE ADDED FOR TRACEABILITY BASED UPON MANUFACTURERS DISCRETION.
- 8 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
PATTERN DEFINED BY CONTACT LAYOUT.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG	J. POLIGNONE	25MAY06	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608
		CHK	G.SKIPPER	25MAY06	
		APP	G.SKIPPER	25MAY06	
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0-PLC $\pm .01$ 1-PLC $\pm .01$ 2-PLC $\pm .02$ 3-PLC $\pm .02$ 4-PLC $\pm .02$ FINISH ANGLES		NAME MALE ASSEMBLY, Z-PACK 2mm HM, TYPE B	
		PRODUCT SPEC 108-19082 APPLICATION SPEC 114-19029		SIZE WEIGHT A1 00779	
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		DRAWING NO C-1645345 RESTRICTED TO -	
CUSTOMER DRAWING		SCALE		4:1 SHEET 2 OF 2 REV A	