

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




20

(C) COPYRIGHT 20 BY -



ALL RIGHTS RESERVED.

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECO-19-007363	13MAY2019	RS	DH
	A2	REVISED PER ECR-20-009164	22JUL2020	MK	DH

VIEW A-A  
SCALE 8:1ROLLS DO NOT  
TOUCHGAP AS REQUIRED TO MEET FORCE  
SPECIFICATIONS AND .018 MAX

1 CONTINUOUS STRIP ON REELS.  
 2 WIRE SIZE #20-#16 AWG  
 3 INSULATION RANGE .090-.130 DIA  
 4 MATING TAB THK. .021-.019  
 5 UL LISTING APPROVAL FOR AWG 20-16  
 6 NOTE REMOVED  
 7 MARKED "F5" IN APPROX. LOCATION SHOWN,  
 TO IDENTIFY AS F-CRIMP AND .020"  
 THICK X .187" PLATING TAB

SECTION C-C  
SCALE 8:1SECTION D-D  
SCALE 8:1

5	TIN FINISH	BRASS MATERIAL	2238207-3 PART NO.
---	---------------	-------------------	-----------------------



TE Connectivity

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASAVARAJA D A CHK HUMPHREY, DAVID APVD HUMPHREY, DAVID	05MAY2018	NAME FASTON 187 STD REC F-CR 20-16 TPBR .020 THK TAB
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	0 PLC ± 1 PLC ± 2 PLC ±.010 3 PLC ± 4 PLC ANGLES ± 5°	05MAY2018 HUMPHREY, DAVID APVD HUMPHREY, DAVID	
PRODUCT SPEC	APPLICATION SPEC	-	-	SIZE CAGE CODE DRAWING NO A300779 C-2238207
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	RESTRICTED TO	SCALE 5:1 SHEET 1 OF 1 REV A2
CUSTOMER DRAWING				