

Wire Wound Type Common Mode Filter




ACM3225F2DV-SERIES-D

1. Features


1. High common mode impedance at high frequency effects excellent noise suppression performance.
2. ACM3225F2DV series realizes small size and low profile 3.2x2.5x2.5 mm
3. 100% Lead(Pb) & Halogen-Free and RoHS compliant.
4. Operating temperature -55~+150°C (Including self - temperature rise)
5. High reliability -Reliability tests comply with AEC-Q200



2. Dimension



Recommended PC Board Pattern



Series	A(mm)	B(mm)	C(mm)	D1(mm)	D2(mm)	L(mm)	H(mm)	G1(mm)	G2(mm)
3225F2DV	3.3±0.2	2.5±0.2	2.5 max	0.55±0.15	0.75±0.20	3.7	2.3	2.2	0.6

Units: mm

3. Part Numbering

ACM	3225	F	2	D	V	-	110	T	03	-	D
A	B	C	D	E	F		G	H	I		J

A: Series

B: Dimension

C: Material

Ferrite Core

D: Number of Lines

2=2 lines

E: Type

W4D

F: Category Code

V=Vehicle

G: Inductance

110=11(μH)

H: Packaging

T=Taping and Reel





I: Rated Current

03=300mA


J: Control S/N

4. Specification

TAI-TECH Part Number	Common mode Impedance (Ω) [10MHz]		Inductance(μH) +50/-30% [100kHz/0.1V]	DC Resistance (Ω) max.	Rated Current (mA) max.	Rated voltage (Vdc) max.	IR (MΩ) min.
ACM3225F2DV-110T03-D	300 min.	550 typ.	11	0.4	300	80	10
ACM3225F2DV-220T02-D	500 min.	1100 typ.	22	0.5	250	80	10
ACM3225F2DV-510T02-D	1000 min.	2600 typ.	51	0.7	200	80	10
ACM3225F2DV-101T01-D	2200 min.	5100 typ.	100	1.5	150	80	10




5. Schematic Diagram



6. MEASURING CIRCUITS 2LINE

Common mode



Differential mode

