

This information is given as an indication. In the continual goal to improve our products, we reserve the right to make any modifications judged necessary

2 W

DC- 15 GHz


SMA

COAXIAL ATTENUATOR

issue
0712B

Page
1 / 1

DRAWING



General tolerances: +/- 0.5 mm

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 15 GHz
IMPEDANCE : 50 Ohms
ATTENUATION - NOMINAL : 11 dB

FREQUENCY	DC- 4 GHz	4 - 8 GHz	8 -12.4GHz	12.4- 15 GHz
V.S.W.R	<= 1.20	<= 1.25	<= 1.30	<= 1.35
DEVIATION (dB)	+0.5 / -0.5	+0.6 / -0.6	+0.7 / -0.7	+0.9 / -0.9

TEMPERATURE SENSITIVITY : $4 \times 10^{-4} \frac{\text{dB}}{\text{dB} \times ^\circ\text{C}}$

PEAK POWER at 25°C (1μs,1%.) : 100 W

AVERAGE POWER at 25°C : 2 W


MECHANICAL CHARACTERISTICS

CONNECTORS : SMA male/female per MIL-C 39012
WEIGHT : < 5 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -55 , +125
STORAGE TEMPERATURE RANGE (°C) : -55 , +125

Power derating
Versus temperature



Specification:

Ericsson -package label -102 01-1003 Uen RevF

QUALITY Dpt app. _____				RADIALl® 101. Philibert Hoffmann - Z.I Ouest - 93116 ROSNY/BOIS Cedex-FRANCE Phone:33.1.49353535 Fax :33.1.48546363 Tvx RADIA 235220F
CREATION PEN : CAT				
EP : -----				
Nom : HS	0712B	Added specif Ericsson	TRIPER	
Date:23. jul.93	ISSUE	REVISIONS	NAME	