



CIRCUIT: SPDT



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. RATING: 5A @ 120VAC OR 28 VDC
2A @ 250 VAC
6. ELECTRIC LIFE: 40,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 Mega-ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ sea level
9. OPERATING TEMP.: -30°C to 85°C
10. 2011/65/EU (ROHS) COMPLIANT
11. ▲ DENOTES CRITICAL PARAMETER

 E-SWITCH®				
TITLE 100SP4T8B13VS3QE				
SCALE 2:1	DATE 9/23/2011	DR BGL	DWG T114801	REV E