






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REF. ONLY.
4. FUNCTION: SPST
5. RATING: 50mA @ 32VDC
- ▲ 6. OPERATING FORCE: 160 ± 50 gf
7. TRAVEL: 0.3 mm
8. CONTACT RESISTANCE: 100 m Ω MAX
- ▲ 9. CONTACT MATERIAL: SILVER
10. DIELECTRIC STRENGTH: 250VAC for 1 min
11. INSULATION RESISTANCE: 10 MEGA Ω min, @ 100VDC
12. ELECTRICAL LIFE: 5,000,000 CYCLES
13. ▲ DENOTES CRITICAL PARAMETER
14. OPERATING TEMP: -40°C to 85°C
15. PACKAGING: TAPE & REEL 1000 PCS



▲ ACTUATOR
COLOR: BROWN



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100296	Release	08/26/21	MW	TITLE TL6150BF160QJ				100118228
					SCALE	DATE	DR	DWG	REV
					5:1	8/26/2021	MW	N615007	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED