

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	E4	REVISED	18SEP17	DZ	SL




DETAIL L
(SCALE 5:1)

(APPLIED TO SHEET 1-2)


- MATERIAL ; HOUSING: HIGH TEMPERATURE THERMO PLASTIC
UL94V-0
CONTACT: COPPER ARROY
LOCK LEVER: STAINLESS STEEL
SOLDER PEG: COPPER ARROY
- FINISH ; CONTACT AREA: GOLD FLASH
ON 0.0013MIN ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLT.
SOLDER PEG: TIN PLATING.


- MECHANICAL KEY POSITION OF CONNECTOR SEE TABLE.
- TOLERANCES NON-CUMULATIVE.
- COPLANARITY : 0.1 MAX.
- THE FLOATING VALUE BY SOLDERING IS NOT INCLUDED.
- NOT MATING CONDITION.

- IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY,
OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE
INSERTED AND LOCKED IN THE LATCH.
- THE SHAPE OF HOUSING AT KEY AREA IS FREE BASICALLY TO
IMPROVE HOUSING WARPAGE

DETAIL H
(SCALE 5:1)DETAIL J
(SCALE 5:1)

GENERAL TOLERANCE
10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

TAPE&REEL	AVAILABLE	2.5V (DDR1)	18.45	1.5	1.8	200	2-1612618-1			
TRAY	AVAILABLE	1.8V (DDR2)	17.55	2.4	2.7	200	1612618-4			
TRAY	AVAILABLE	2.5V (DDR1)	18.45	1.5	1.8	200	1612618-1			
PACKING TYPE	TOOLING STATUS	POWER SUPPLY (TYPE)	D5	D4	D3	POS	PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.TANIGAWA 210CT02	TE TE Connectivity							
		CHK H.KODAMA 210CT02								
		APVD I.ENOMOTO 210CT02	NAME DDR1 & DDR2 SODIMM SOCKET 0.6mm PITCH 200POS -							
		PRODUCT SPEC -								
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± ± 3 PLC ± ± 4 PLC ± - ANGLES ± ±		APPLICATION SPEC -			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				WEIGHT -			A3	00779	C-1612618	-
				CUSTOMER DRAWING						
				SCALE						
MATERIAL		FINISH		1 OF 5			F4			





(APPLIED TO SHEET 3)


- 1 TOLERANCES ON ALL DIMENSIONS ± 0.15 UNLESS OTHERWISE SPECIFIED.
- 2 P.C. BOARD THICKNESS APPLIES ACROSS TABS AND INCLUDES PLATING AND/OR METALIZATION.
- 3 FINISH OF PAD : GOLD PLATING 0.00076 MIN. OVER Ni PLATING 0.002MIN.

 NO BURR.

 CHAMFER 0.25 MAX x 45° IF EXIST.



DETAIL C
SCALE 8:1 (BACK SIDE)



1.9 MAX.

1.9 MAX.

1.9 MAX.

1.9 MAX.


(1)

DETAIL D

SCALE 8:1

推奨基板仕様
RECOMMENDED MATING P.C.B CONFIGRATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
		CHK			
DIMENSIONS: MM		APVD		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		DDR1 & DDR2 SODIMM SOCKET	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± ±		APPLICATION SPEC		0.6mm PITCH 200POS	
MATERIAL		WEIGHT		SIZE	RESTRICTED TO
		—		A3	—
FINISH		—		CAGE CODE	DRAWING NO
				00779	C-1612618
CUSTOMER DRAWING				SCALE	REV
				NTS	F4
				SHEET	3 OF 5



THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—



1. THE DIRECTION OF EACH CONNECTOR ON THE EMBOSS IS REFERENCED TO THIS DRAWING.

2. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$.

PULL OUT DIRECTION →




120	2	240	2-1612618-1
PCS/REEL	REEL/CARTON	PCS/CARTON	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	$\pm -$
1 PLC	$\pm -$
2 PLC	± 0.5
3 PLC	± 0.5
4 PLC	$\pm -$
ANGLES	$\pm 3^\circ$
FINISH	

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

DDR1 & DDR2 SODIMM SOCKET
0.6mm PITCH 200POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-1612618

SCALE 1:2

SHEET 5 OF 5

REV E4