

PART NUMBER	ITEM ① BODY	ITEM ② CONTACT	ITEM ③ INSULATOR	ITEM ④ CRIMP SLEEVE	ITEM ⑤ CUPLING NUT
27-9105	BRASS NICKEL PLATED	BRASS GOLD PLATED	DELRIN	BRASS NICKEL PLATED	ZINC NICKEL PLATED

受控 CONTROLLED DOCUMENT

编号
P/N

27-9105

版本
Rev

01

日期
Rel'd Date

May8,09

DRAWING NO.
27-9105

REVISIONS

01

OFFICIAL RELEASE

04-05-09

T

W




T

Thomas Chow

2009.05.04


14:41:52

+08'00'



NOTES:

1. IMPEDANCE: 50 OHMS NOMINAL
2. FREQUENCY RANGE: 0-4 GHz
3. CABLE ACCEPTABILITY: RG174, RG187, RG188, RG316
4. CABLE RETENTION: 20lbs MIN
5. RECOMMENDED TEMPERATURE RANGE: -55 °C TO +85°C
6. FURTHER TECHNICAL DETAIL: REFER TO EMERSON DOCUMENT P/N 27-0000



THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1994

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY TERRY.W	DATE 04-05-09
DECIMALS	mm	CHECKED BY TERRY.W	DATE 04-05-09
X	± 0.5	APPROVED BY THOMAS	DATE 04-05-09
X.X	± 0.2		
X.XX	± 0.05		
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

EMERSON Network Power		Connectivity Solutions	
TITLE BNC MALE CRIMP FOR RG174/U		SHEET 1 OF 1	
DRAWING NO. 27-9105		SIZE C	