








DIM		TOL			
		2P--6P	7P--12P	13P--18P	19P--24P
Dim L	N×3.5+0.70	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×3.5	±0.15	±0.20	±0.30	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material:
- Item (A) Lever: Thermoplastic (UL 94V-0)
 - Item (B) Terminal housing: Thermoplastic (UL 94V-0)
 - Item (C) Wire guard: Stainless steel
 - Item (D) Solder Pin: Brass.Tin plated

- Electrical: cULus
- Voltage rating: 300 V
 - Current rating: 10 A
 - Wire range:
 - Solid wire(AWG): 16-24
 - Stranded wire(AWG): 16-24
 - Wire strip length: 12-13 mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval:

NM xx 1 0 x 1 xxxx G

- No. OF POLES
- 02 2 CONTACTS
 - 03 3 CONTACTS
 -
 - 24 24 CONTACTS
- Color
- 0 Black (RAL9005)
 - 3: Orange (RAL 2011/P)
 - 5: GREEN (RAL 6018/T)
 - 6: Blue (RAL5015/A)
 - 8: GREY (RAL 7004/P)
- G: Pb<40000ppm
- A000: "@" Logo (Standard)
- A00A: "ANYTEK" Mark
- Any special item by customer request. please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NM 3.5 Series Horizontal 180° wire inlet			
PART NO.	NMxx10x1xxxxG			DWG NO.	8NM0301
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2011.10.27	Chen Bo 2011.03.31		Tolerance
					X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°
				SHEET: 01/01	REV.: A2