






SCHEMATIC



SPECIFICATIONS

FUNCTION:
Pole 1: Off-On
Pole 2: Off-On
RATINGS:
10A 125VAC [cULus]
6(2)A 250V~ T125 1E4 [VDE]
CONTACT RESISTANCE:
Initial: 35mΩ at 50VAC Min.
INSULATION RESISTANCE:
100MΩ at 500VDC Min.
DIELECTRIC STRENGTH:
1500VAC For 1 Minute
ELECTRICAL LIFE:
10,000 Cycles Min.
TEMPERATURE:
Operating: -20°C to 105°C [UL, cUL]
-20°C to 125°C [VDE]




MATERIALS

BODY:
Polyamide 6/6 (PA66), UL94 V-2
ACTUATOR/LENS:
Polyamide 6/6 (PA66), UL94 V-2
LAMP LENS:
N/A
LAMP:
N/A
SPRING:
Steel
BALL:
Steel

COLORS AND MARKINGS

BODY:
Black
ACTUATOR/LENS:
Pole 1: Black
Pole 2: Black
MARKINGS:
Pole 1: I/O Vertical
Pole 2: I/O Vertical
MARKING COLOR:
Pole 1: White
Pole 2: White

SUGGESTED PANEL CUTOUT



PANEL THICKNESS	X
0.030~0.049 [0.75~1.25]	0.756 [19.2]
0.049~0.079 [1.25~2.00]	0.764 [19.4]
0.079~0.118 [2.00~3.00]	0.772 [19.6]

MOBILE CONTACT:
Silver Plated Copper
CONTACTS:
Silver Plated Copper
TERMINALS:
Silver Plated Copper

REV.	DATE	BY
1		

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH-LAMB INDUSTRIES AND IS NOT TO BE COPIED OR TRANSMITTED

REV.

NEW RELEASE DESCRIPTION

2015 10/9/12

DATE

SCALE


PROJECTION

DATE

10/9/12

REVISION

A



RA21131121

38-RA21131121

DATE

A