

● 20-WAY FIXED CONNECTORS

4 Versions:	12 mm between axes	Solder outlet
		Pin outlet
	6 mm between axes	Solder outlet
		Pin outlet

These connectors contain twenty 2 mm dia. sockets moulded into an insulated monobloc of low bulk. The low pitch between sockets makes them particularly suitable for use in circuit breakers and test batteries.

ADVANTAGES : QUICKER ASSEMBLY TIME

Sockets are no longer mounted individually (connected to block with 5 screws)

Simplified panel piercing

Orientation of solder shafts


Possibility of removing the cable harness without disconnecting each socket.

CHARACTERISTICS

– Insulation resistance	:	$\geq 5\,000\,M\Omega$
– Current rating max	:	7 A (at 20°C)
– Operating voltage	:	500 V rms 50 Hz
– Operating temperature	:	– 40°C + 125°C
– Material		
<i>metallic parts</i>	:	brass
<i>plating</i>	:	gold
<i>Insulation</i>	:	self-extinguishable PBT UL 94 Vo.

► Packaging Individually.

✎ SOLDER OUTLET

Part number	Dimensions (12 mm between axes)
R 929 991 000 / Blue R 929 991 001 / Red R 929 991 002 / Green R 929 991 003 / Black R 929 991 004 / Yellow	 Drilling jlg : R 282 906 * Panel piercing dimension: (thickness: 2 mm maximum) 20 holes 5 dia. (contacts) – 5 holes 3 dia. (fixing)

* Made to order product, please consult Radiall for price and delivery