




NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @ 12VDC
- ▲ 5. OPERATING FORCE: 250 ± 50 gf
6. TRAVEL: 0.25 +0.2 / -0.1 mm
7. CONTACT RESISTANCE: 100 Milli-OHMS max.
8. DIELECTRIC STRENGTH: 250V RMS min.
9. INSULATION RESISTANCE: 100 Mega-OHMS min.
10. LIFE EXPECTANCY: 1,000,000 CYCLES min.
- ▲ 11. CONTACT MATERIAL: GOLD
12. OPERATING TEMP: -40°C TO 85°C
13. ▲ DENOTES CRITICAL PARAMETER



B	24547	CHANGE OPERATING TEMPERATURE	10/6/20	JM
A	18661	Released For Production	9/30/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL1105LF250R

SCALE 4:1

DATE 9/30/2009

DR BLR

DWG P010230

REV B