




Fig. 1




Fig. 2




Fig. 3





Fig. 4

- Series 41X double row strip sockets are on 2,54 grid.
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. Using Mill-Max #1001, 0134, 0501 or 1534 pins (See pages 132, 133, 136) for details.
- Hi-Rel, 4-finger BeCu #12 & #30 contacts are rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1	Series 410...001	Standard Solder Tail
	410-XX-2_ _-41-001000	Specify # of pins → 02-64
Fig. 2	Series 411...001	Long Solder Tail
	411-13-2_ _-41-001000	Specify # of pins → 02-64
Fig. 3	Series 415...001	Very Low Profile
	415-XX-2_ _-41-001000	Specify # of pins → 02-64
Fig. 4	Series 415...003	Ultra Low Profile
	415-XX-2_ _-41-003000	Specify # of pins → 02-72

For Electrical, Mechanical & Environmental Data, See pg. 4

XX=Plating Code See Below

For RoHS compliance select ◇ plating code.

SPECIFY PLATING CODE XX=	13◇	93	43◇
Sleeve (Pin)	0,25µm Au	5,08µm Sn/Pb	5,08µm Sn
Contact (Clip)	0,76µm Au	0,76µm Au	0,76µm Au