

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2011

© COPYRIGHT 2011

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

AI

-




A

REVISED PER ECO-12-002880

14FEB12

KH

MS



MATERIALS

HOUSING-POLYAMIDE, COLOR-GREEN

LEVER-POLYAMIDE, COLOR ORANGE

CONTACT SPRING-COPPER ALLOY-LEAD FREE TIN PLATED

CLAMPING SPRING-STEEL

MECHANICAL

INSERTION FORCE PER POLE- 3 NEWTON MAX

WITHDRAWAL FORCE PER POLE- 1.5 NEWTON MIN

STRIPPING LENGTH- 10.5 TO 11.5 MM

OPERATING TEMPERATURE--40°C TO +110°C



ELECTRICAL

WIRE SIZE= 30 TO 14 AWG SOLID OR STRANDED

VOLTAGE RATING- 300 VOLTS

CURRENT RATING- 11 AMP STRANDED; 9AMP SOLID

CONTACT RESISTANCE-15 MILLOHM MAX

INSULATION RESISTANCE-10⁹ OHMS MIN (500V DC)

84.00	87.50	25	2-1986692-5
80.50	84.00	24	2-1986692-4
77.00	80.50	23	2-1986692-3
73.50	77.00	22	2-1986692-2
70.00	73.50	21	2-1986692-1
66.50	70.00	20	2-1986692-0
63.00	66.50	19	1-1986692-9
59.50	63.00	18	1-1986692-8
56.00	59.50	17	1-1986692-7
52.50	56.00	16	1-1986692-6
49.00	52.50	15	1-1986692-5
45.50	49.00	14	1-1986692-4
42.00	45.50	13	1-1986692-3
38.50	42.00	12	1-1986692-2
35.00	38.50	11	1-1986692-1
31.50	35.00	10	1-1986692-0
28.00	31.50	9	1986692-9
24.50	28.00	8	1986692-8
21.00	24.50	7	1986692-7
17.50	21.00	6	1986692-6
14.00	17.50	5	1986692-5
10.50	14.00	4	1986692-4
7.00	10.50	3	1986692-3
3.50	7.00	2	1986692-2
DIM X	DIM L	POLE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 12JAN2012

CHK KIRAN HOLAL

APVD MIKE SARVER

APVD MIKE SARVER

PRODUCT SPEC

-

APPLICATION SPEC

-


WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.40
2 PLC	±0.20
3 PLC	±
4 PLC	±
ANGLES	±1°

MATERIAL

-

FINISH

-

STE

TE Connectivity

NAME

STRAIGHT SPRING TYPE PLUG CONNECTOR
SIDE STACKABLE RIGHT
02 - 25 POLES PITCH 3.50mm

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1986692

-

SCALE 2:1

SHEET 1 OF 1

REV A