




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.


MARKETING SALES DRAWING DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING DIMENSIONS IN METRIC - []




NOTES:

1. TUSONIX STANDARD PART NUMBER: 4600-053.
TUSONIX RoHS COMPLIANT PART NUMBER: 4600-053 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. MATERIALS:
BUSHING - TIN PLATED STEEL.
LEAD STANDARD PART; SOLDER PLATED COPPER.
RoHS PART; SILVER PLATED COPPER.
NUT - TIN PLATED BRASS.
L"WASHER - TIN PLATED PHOSPHOR BRONZE.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. MOUNTING TORQUE: 8 lb - ins. max.
5. DCR - .01Ω max.
6. MAX. SOLDER TEMPERATURE 500°F.

MOUNTING HARDWARE



LOCK WASHER



HEX NUT

MIN. Cx (μF)	WVDC		CURRENT DC (AMPS)	D.W.V. (VDC)	I.R. MIN.	MIN. NO LOAD INSERTION LOSS (dB) PER MIL-STD 220 @ +25°C						TEMP. CHARA.
	85°C	125°C				30 KHz	100 KHz	300 KHz	1 MHz	10 MHz	1GHz	
1.4	80	50	15	300	500 M Ω	15	25	34	44	60	70	X7R

X-2015 Rev-0

REVISION RECORD					--TOLERANCES-- Unless Otherwise Specified DECIMAL ±  ANGLES ±  TUSONIX TUCSON, ARIZONA		Title COAXIAL BROADBAND - "L"		Drawn S.M. 08-19-02		Scale 2 X	
Original Release C.O. 930129-1 -066 ADDED 0-400 TO 125°C. S.M. 11-18-97		4 REVISED DWG & DRAWING MADE FOR EACH VAR. S.M. 08-19-02		5 20020819-3-01 REVISED & ADDED NOTES. S.M. 01-05-06			6 20060104-3-01					
								Approved B.Mc. 08-19-02		A 4600-053		