




REV. 0

DCO 143374

COIL: @ 25°C

RESISTANCE 800 OHMS ±10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 4.0 VDC MAX, 0.64 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 2.5 MS MAX

CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. B.D. 12/19/01

12/19/01

CII Technologies
advanced control electronic solutions

CUST. QPL

CUST. NO. M39016/41-035M REV.

"JMGS" RELAY

JMGSC-12M