


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PUI AUDIO, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PUI AUDIO, INC. IS PROHIBITED.
© 2010, PUI AUDIO Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.25	W
MAX INPUT POWER	0.5	W
IMPEDANCE	100±15%	OHM
OUTPUT SPL @ 0.1W/0.1M (AVG. 0.8, 1.0, 1.2, 1.5kHz)	90±3	dBA
DISTORTION (MAX.)	5%	—
RESONANT FREQUENCY	700±20%	Hz
FREQUENCY RANGE	F _o ~ 5,000	Hz
HOUSING MATERIAL	METAL	—
CONE MATERIAL	MYLAR	—
MAGNET MATERIAL	NdFeB	—
OPERATING TEMPERATURE	-20 ~ +85	°C
WEIGHT	3	grams

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	6/29/15	
A	ADD METAL COVER TO DRAWING	2/28/20	M.L.




NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS.
- SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.
- THIS PART IS RoHS 2015/863/EU COMPLIANT.

FILE NAME
AS020100MR-R.DWG

UNLESS OTHERWISE SPECIFIED:
ALL PURCHASES ARE SUBJECT TO THE PUI AUDIO
TERMS AND CONDITIONS SALE FOUND AT
http://www.puiaudio.com/pdf/terms_conditions.pdf
(paper copy available upon request).
DIMENSIONS ARE IN MILLIMETERS. TOLERANCES ARE
±0.5 AND ANGLES ARE ±3°.



3541 Stop Eight Road
Dayton, Ohio 45414

APPROVALS	DATE	SIZE	DRAWING NO.
DRAWN <i>M.L.</i>	6/15	A	AS020100MR-R
CHECKED <i>M.L.</i>	6/15		
APPROVED <i>B.R.</i>	6/15		
SCALE: N.T.S.		SHEET 1 OF 1	

SPEAKER