





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	ECR-21-123888	16DEC2021	DC	FL
			C1	ECR-22-126910	21JAN2022	DC	FL
			C2	ECR-22-128794	10FEB2022	DC	FL



P/N 0-284930-3 AS SHOWN

- ① WIRE RANGE : STRANDED 0.22-0.35 mm² (INS. DIA. 1.30±0.1)
- ② MATING PART: TAB HEADER P/Ns 1971817, 1971818 AND EQUIVALENT;
PCB FRAME P/N 964575 (PCB THK 1.5±0.14 COPPER CLADDING INCLUDED)
SEE PRODUCT SPEC. 108-18056 FOR FRAME APPLICATION
- ③ KEYING RIBS TO BE REMOVED BY TERMINATION MACHINE
- ④ CUT OFF DIMENSION DUE TO PRODUCTION PROCESS
- ⑤ CIRCUIT No. IDENTIFICATION
- ⑥ TYCO ELECTRONICS TRADEMARK (OPTIONAL POSITION)
- ⑦ TAMPOGRAPHIC COLOUR CODE AREA
(P/Ns IDENTIFICATION BEFORE CRIMPING)
- ⑧ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ⑨ PBT GF
- ⑩ PA GF, UL94-V0 & GWEPT 750°C NO FLAME, NATURAL
- ⑪ PRELIMINARY PN NOT FOR PRODUCTION
- ⑫ ALTERNATIVE RESIN PBT GF
- ⑬ PART RELEASED WITH PARTIAL VALIDATION AND PENDING AGENCY APPROVALS
- ⑭ (REPLACES NOTE 10) PBT GF, UL94-V0 & GWEPT 750°C NO FLAME, NATURAL

OBsolete	NATURAL	13	30.0	34.9	5x	1-284930-3	-	1-2402726-3
	-	11	25.0	29.9	6x	1-284930-1	2311501-1	1-2402726-1
OBsolete	NATURAL	10	22.5	27.4	6x	1-284930-0	-	1-2402726-0
	NATURAL	9	20.0	24.9	7x	284930-9	-	2402726-9
OBsolete	NATURAL	8	17.5	22.4	8x	2-284930-8	-	2-2402726-8
	-					0-284930-8	2311500-8	2402726-8
	-					0-284930-7	2311500-7	2402726-7
	BLUE					2-284930-6	2311500-6	2-2402726-6
	-	6	12.5	17.4	10x	0-284930-6	2311500-6	2402726-6
OBsolete	NATURAL					2-284930-5	-	2-2402726-5
	-	5	10.0	14.9	11x	0-284930-5	2311500-5	2402726-5
OBsolete	NATURAL					3-284930-4	-	3-2402726-4
	RED	4	7.5	12.4	13x	2-284930-4	2311500-4	2-2402726-4
	-					0-284930-4	2311500-4	2402726-4
OBsolete	NATURAL					5-284930-3	-	5-2402726-3
OBsolete	BLUE	3	5.0	9.9	16x	4-284930-3	-	4-2402726-3
OBsolete	BROWN					3-284930-3	-	3-2402726-3
	GREEN					2-284930-3	2311500-3	2-2402726-3
	-					0-284930-3	2311500-3	2402726-3
	COLOUR CODE	HSG POS	DIM. A	DIM. B		TE P/N	TE P/N	TE P/N

SEE TABLE	-	-	-	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG REV	FABRIS	27FEB2004	 TE Connectivity		
	PH. BRONZE, TIN PLATED	IDC RECEPTACLE CONTACT	2	DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPROVED	G. TURCO	27FEB2004		NAME	
	PBT GLASS FIBER FILLED	FEMALE HOUSING	1		0 PLC ± 0.2 1 PLC ± 0.2 2 PLC ± 0.2 3 PLC $\pm$ 4 PLC $\pm$	PRODUCT SPEC	108-18056	APPLICATION SPEC		114-18049-1	
Q.TY	MATERIAL	DESCRIPTION	ITEM		ANGLES				FINISH		RESTRICTED TO
REVISIONE DELL'ASSEMBLAGGIO (REVISION OF EACH ASSY NO)				MATERIAL SEE TABLE		CUSTOMER DRAWING	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
ELENCO DEI COMPONENTI (PARTS LIST)							A1	00779	C=284930	-	
0.14" PER ASSEMBLAGGIO (0.14" PER ASSY)								SCALE	5:1	SHEET 1 OF 1	REV C2