







NOTES

- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
 - 3 - CIRCUIT DIAGRAM, CATALOG LISTING, AND DATE CODE ARE SHOWN ON NAMEPLATE
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS:
.010 OF PLUNGER TRAVEL

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE-----	6-12 LB	CONTACT ARRANGEMENT S P D T (2)		DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE----	30 LB MAX			UNLESS OTHERWISE NOTED
RELEASE FORCE-----	4 LB MIN	28 VDC		DIMENSIONS ARE IN INCHES
PRETRAVEL-----	.040 MAX	LOAD	SEA LEVEL	TOLERANCES ARE:
DIFFERENTIAL TRAVEL----	.020 MAX	RES	4	ONE PLACE (.0) ±.030
OVERTRAVEL-----	.250 MIN	IND	2	TWO PLACE (.00) ±.015
		MOTOR	4	THREE PLACE (.000) ±.005
				ANGLES ±
				WEIGHT 19.5 OZ MAX