

“Marshal Bean”
Protective Rubber Covers with Tether Rope
780-555



**Fits Metal Shell
M83513 Type
Connectors**

**Rubber Covers for Tactical
Equipment and Field Instruments**

— These friction-fit covers provide dust and splash protection.

Two Tether Styles — Choose ring terminals for attachment to a panel, or choose slip knots for cable attachment.

-55° to +125° Temperature Range

MATERIALS & FINISHES



Cover	SBR Rubber Per ASTM D2000 Type C
Cord	Nylon Per MIL-C-43307
Ring Terminal	Stainless Steel
Slip Collar	Kynar
Crimp Ring	Copper, Black Oxide Finish

HOW TO ORDER 780-555 RUBBER PROTECTIVE COVERS

Series	Connector Layout	Nylon Cord Option	Nylon Cord Length	Attachment Option	Rubber Type
780-555	9P 9S	Omit — (leave blank)	Length in One Inch Increments	Ring Terminal	Omit
	15P 15S	Cover only, no cord		06 — .125 (3.2) I.D. 01 — .140 (3.6) I.D. 05 — .167 (4.2) I.D. 04 — .197 (5.0) I.D.	Standard Rubber
	21P 21S				
	25P 25S	G — Nylon Cord	Example: "6" equals six inches. ± .250 Inches ± 6.35 mm	SK — Slip Knot	C Conductive Rubber
	31P 31S				
	37P 37S				
	51P 51S				
	51-2P 51-2S				
	67P 67S				
	69P 69S				
	100P 100S				

Sample Part Number

780-555 37P G 4 – SK



Layout	A Max.		B Max.	
	In.	mm.	In.	mm.
9P, 9S	.830	21.08	.370	9.40
15P, 15S	.980	24.89	.370	9.40
21P, 21S	1.130	28.70	.370	9.40
25P, 25S	1.230	31.24	.370	9.40
31P, 31S	1.380	35.05	.370	9.40
37P, 37S	1.530	38.86	.370	9.40

Layout	A Max.		B Max.	
	In.	mm.	In.	mm.
51P, 51S	1.480	37.59	.410	10.41
51-2P, 51-2S	1.880	47.75	.370	9.40
67P, 67S	2.770	70.36	.370	9.40
69P, 69S	1.780	45.21	.410	10.41
100P, 100S	2.215	56.26	.460	11.68

Standard material contains trace amounts of sulfur (a vulcanizing agent) which is known to contribute to degradation/corrosion of silver plated components such as braid, etc. Specify MOD Code suffix -675 for sulfur-free material.

© 2011 Glenair, Inc.

CAGE Code 06324

Printed in U.S.A.