





**DESCRIPTION:** 97 SERIES SOLDER STYLE PANEL & CABLE MOUNT  
**D-SUB CONNECTORS**  
**MODEL NUMBER:** 40-97XXS  
**APPLICATION:** FOR CABLE  
**CRIMP TOOL:** N/A  
**IMPEDANCE:** N/A  
**FEQUENCY RANGE:** 0-15 MHz  
**MATERIAL:** HOUSING STEEL NICKEL PLATED  
 INSULATOR PBT+FIBER-GLASS UL94-V0 WHITE  
 CONTACT COPPER-ALLOY, GOLD PLATED  
**RoHS COMPLIANCE:** YES  
**TECHNICAL DETAIL:** N/A



**DIM OUTLINE**

MODEL NUMBER	PIN	A	B	C	D
40-9709S	09	30.80	24.99	16.30	19.20
40-9715S	15	39.15	33.32	24.65	27.70
40-9725S	25	53.00	47.04	38.40	41.10
40-9737S	37	69.30	63.50	54.80	57.30

 <small>This PROPRIETARY Document is property of Emerson Network Power, Connectivity Solutions. It is not transferable and is issued with restrictions. The information contained herein is not to be reproduced, distributed, or transmitted in whole or in part, in any manner, without the prior written permission of Emerson Network Power, Connectivity Solutions. Requests for permission should be submitted in writing to: Emerson Network Power, Connectivity Solutions, 2002/95/EC, 2002/95/EC</small>	3RD ANGLE PROJECTION	<b>AIM-Cambridge</b> <small>Title: D-Sub Connector, 97 Series, Solder Style Panel and Cable Mount, Female</small>	
	RoHS <input checked="" type="checkbox"/>	Model No.	40-97XXS
	2002/95/EC	Size	DO NOT SCALE
	UNLESS OTHERWISE SPECIFIED	DRAWING	Date: 9/9/2013
	.XX ± .51		Sheet 1 of 1
	.XXX ± .127		
	ANGLES ± 2°		