

BULKHEAD FEEDTHROUGH STRAIGHT JACK, FULL CRIMP TYPE, FOR FLEXIBLE CABLE





Fig. 1






Fig. 2

cable group	part number	fig.	A	B	C	mounting	panel drilling	finish	note
2 / 50 / S	R124 310 020	1				M 03	P 08	BBR	Reverse crimping / Solder contact
2 / 50 / S	R124 310 023	1				M 03	P 08	Gold	
2.6/ 50 / S	R124 312 120	2	22,4	1,61	3,25	M 01	P 01	BBR	3 piece SMA
2.6/ 50 / S	R124 312 123	2	22,4	1,61	3,25	M 01	P 01	Gold	
2.6/ 50 / D	R124 313 120	2	22,4	1,61	3,5	M 01	P 01	BBR	
2.6/ 50 / D	R124 313 123	2	22,4	1,61	3,5	M 01	P 01	Gold	
5 / 50 / S	R124 314 120	2	25,4	3,11	5,41	M 01	P 01	BBR	3 piece SMA
5 / 50 / S	R124 314 123	2	25,4	3,11	5,41	M 01	P 01	Gold	
5 / 50 / D	R124 315 120	2	25,4	3,11	5,8	M 01	P 01	BBR	
5 / 50 / D	R124 315 123	2	25,4	3,11	5,8	M 01	P 01	Gold	

**BULKHEAD FEEDTHROUGH STRAIGHT JACK, SOLDER TYPE, FOR SEMI-RIGID CABLE
(PANEL SEAL)**



cable group	part number	A	mounting	panel drilling	finish	note
.085	R124 326 000	2,25	M 04	P 01	BBR	Non captivated center contact
.085	R124 326 003	2,25	M 04	P 01	Gold	
.141	R124 325 000	3,65	M 04	P 01	BBR	
.141	R124 325 003	3,65	M 04	P 01	Gold	