





RECOMMENDED P.C.B. LAYOUT
SCALE 1X

RECOMMENDED MOUNTING
SCALE 1X




SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
DN	NONE	DN
2-3,5-6 8-9	OPEN	2-1, 5-4 8,7

NOTES:


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.XX=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 28VDC; 2A @250VAC.
5. CONTACT MATERIAL: Copper Alloy w/Silver Plating.
6. ELECTRICAL LIFE: 40,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to 85°C
10. 2002/95/EC (ROHS) COMPLIANT

B	16879	ADD BLK LABEL,TITLE	1/17/2007	TN
A	14464	RELEASED FOR PRODUCTION	11/5/04	AR
REV.	ECN NO.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED



SECTION A-A



TITLE		DATE		DR		DWG		REV	
3003P1R6BLKM7QEBLK		1/17/2007		TN		T331028		B	
SCALE		1.5:1							

