




REV. 0
DCO 143778


COIL: @ 25°C
RESISTANCE 100 OHMS $\pm$ 10%
NOMINAL VOLTAGE 5.0 VDC
MUST OPERATE 2.6 VDC
MUST RELEASE 1.4 VDC MAX. 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX
RELEASE TIME 7.5 MS MAX
CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 21AUG03

8/22/03

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/16-041M REV.

"JM5D" RELAY

JM5CD-5XMS