







LOC		DIST		REVISIONS				
AD	00	P	LYR	DESCRIPTION	DATE	OWN	APVD	
			B	REVISED PER ECO-11-025276	05JAN2012	KH	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.



THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. K. SHOBER 31JAN2011	 TE Connectivity	
DIMENSIONS:		CHK J. EABY 31JAN2011		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. EABY 31JAN2011	NAME	
		PRODUCT SPEC	IMPACT, 2 PAIR, 16 COLUMN, HEADER	
	0 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ±	APPLICATION SPEC	RIGHT GUIDED, OPEN END WALL	
		WEIGHT	SIGNAL MODULE, 0.39 PTH	
MATERIAL 	FINISH SEE TABLE	SIZE CAGE CODE DRAWING NO		RESTRICTED TO
		A100779C-2057741		-
CUSTOMER DRAWING		SCALE 6:1	SHEET 1 OF 2	REV B

LOC	DIST	REVISIONS					
AD	00	REV	LYR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-

	5.5	2057741-6
	4.9	2057741-5
	4.5	2057741-4
	5.5	2057741-3
	4.9	2057741-2
	4.5	2057741-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 31 JAN 2011	TE Connectivity		
DIMENSIONS:		CHK J. EABY 31 JAN 2011			
mm		APVD J. EABY 31 JAN 2011	NAME IMPACT, 2 PAIR, 16 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC		
		0 PLC ±	APPLICATION SPEC		
		1 PLC ±0.25	SIZE CAGE CODE DRAWING NO		
		2 PLC ±0.13	RESTRICTED TO		
MATERIAL		3 PLC ±	A100779C=2057741		
FINISH		4 PLC ±	CUSTOMER DRAWING		
SEE TABLE		ANGLES	SCALE 5:1 SHEET 2 OF 2 REV B		