









SECTION A-A
SCALE 4:1



SECTION B-B
SCALE 4:1


spec ref		dr		Hai-Ling Liu	2015/03/30	projection		MM		size	A2	scale	1:1		
tolerance std		eng		Hai-Ling Liu	2015/05/11					ecn no		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr		Terris Liu	2015/05/11					product family				rel level	
		appr		Pei-Ming Zheng	2015/05/11										
surface		linear	0.X	±0.5		title	HPCE BTB RAH UNIVERSAL DRAWING				dwg no	10134214		rev	A
			0.XX	±0.25											
			0.XXX	±0.1											
		angular	0°	±2°											

PDS: Rev :A

STATUS:Released

Printed: May 12, 2015


CONTACT TYPE	TOP LAYER DESCRIPTION	TABLE 1 (HPCE / SOLDER TAILS) PLATED THROUGH-HOLE REQUIREMENTS				
		DRILLED HOLE DIAMETER	COPPER THICKNESS	TIN-LEAD THICKNESS	TIN THICKNESS	FINISHED HOLE DIAMETER
POWER	TIN-LEAD	1.10-1.16 (1.15 DRILL)	0.025 - 0.050	0.005 - 0.015	--	0.94 - 1.10
	IMMERSION TIN	1.10-1.16 (1.15 DRILL)	0.025 - 0.050	--	0.9 - 1.5um	0.94 - 1.10
	COPPER (SEE NOTE 8)	1.10-1.16 (1.15 DRILL)	0.025 - 0.050	--	--	0.94 - 1.10
SIGNAL	TIN-LEAD	0.93-0.99 (0.98 DRILL)	0.025 - 0.050	0.005 - 0.015	--	0.77 - 0.93
	IMMERSION TIN	0.93-0.99 (0.98 DRILL)	0.025 - 0.050	--	0.9 - 1.5um	0.77 - 0.93
	COPPER (SEE NOTE 8)	0.93-0.99 (0.98 DRILL)	0.025 - 0.050	--	--	0.77 - 0.93



TOP SURFACE
RECOMMENDED PCB LAYOUT

dr	Hai-Ling Liu	2015/03/30	projection	MM	size	A2	scale	1:1									
eng	Hai-Ling Liu	2015/05/11			ecn no	-	-										
chr	Terris Liu	2015/05/11															
appr	Pei-Ming Zheng	2015/05/11															
product family			rel level														
			Released														
FCi			title			HPCE BTB RAH	UNIVERSAL DRAWING	dwg no	10134214	rev	A						
www.fci.com			cat. no.														
Product - Customer Drw			sheet 2 of 3														

10134214 - MM NN PP LF



	A	B	C	D
TAIL LENGTH(DIM T)	2.60		3.25	
HOLD-DOWN PEGS OPTION	Y	N	Y	N

LEAD FREE


DIM	TABLE 2. LENGTH FORMULAS
DIM A II	$(MM + NN) / 2 \times 2.54 + (PP / 2) \times 1.27 + 16.02$
DIM B	$DIM A - 7.5$
DIM T	2.60 OR 3.25

Example: The configuration above is 10134214-241224CLF
STD HPCE BTB R/A HEADER 36P24S with Hold-Down Pegs.
24P is 4 beam contact, 12P is 2 beam contact.

TABLE 3: PART NUMBER CODE. HPCE BTB R/A HEADER P+S CONFIG

NOTES:

- CONNECTOR MATERIALS:
HOUSING: HIGH TEMPERATURE THERMAL PLASTIC, BLACK UL 94V-0 COMPLIANT
CONTACTS: HIGH PERFORMANCE COPPER ALLOY.
- CONTACT FINISH REF. GS-12-1031 SECTION TBD
- PRODUCT SPECIFICATION: GS-12-1125
- APPLICATION SPECIFICATION: GS-20-0388
- PRODUCT MARKING (FCI PART NUMBER & DATE CODE) ON HOUSING IN AREA SHOWN.
- PACKAGING MEETS FCI SPECIFICATION GS-14-2272.
- HOUSING COMPONENT WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 60 SECONDS IN A CONVECTION, INFRA-RED, OR VAPOR PHASE REFLOW OVEN.
- COPPER PLATING THICKNESS IN CENTER OF VIA-HOLE CAN BE NO MORE THAN 0.003 LESS THAN OTHER AREAS.
- ALL HOLE SIZES ARE FINISHED HOLE SIZES.
- MOUNTING HOLES ARE UNPLATED
 $\varnothing 2.20 \pm 0.05$ FOR SOLDER TAILS
- MAXIMUN OVERALL LENGTH IS 100 mm



dr	Hai-Ling Liu	2015/03/30		MM		size	A2	scale	1:1			
eng	Hai-Ling Liu	2015/05/11				ecn no	-	rel level	Released			
chr	Terris Liu	2015/05/11										
appr	Pei-Ming Zheng	2015/05/11	product family		-							
		title	HPCE BTB RAH			dwg no	10134214			rev	A	
			UNIVERSAL DRAWING									
www.fci.com		cat. no.	-	Product - Customer Drw						sheet 3 of 3		

PDS: Rev :A

STATUS:Released

Printed: May 12, 2015