







▲ LED #2 AMBER
LENS: WHITE


▲ LED #1 RED
LENS: WHITE

BLACK ACTUATOR
MATERIAL:
SOFT TPR (Rubber)



▲

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	OFF	ON
1-2	NONE	2-3



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. RATING: 16A @ 30VDC, 50/60 Hz, μ T85/55
UL LISTED
5. ELECTRICAL LIFE: 10,000 CYCLES
6. MECHANICAL LIFE: 30,000 CYCLES
7. CONTACT RESISTANCE: <20 MILLI-OHMS INITIAL
8. DIELECTRIC STRENGTH: >1,500V AC 1MIN
9. INSULATION RESISTANCE: >100 MOHMS @ 500VDC
10. OPERATING TEMP: 0°C to 55°C
11. LED VOLTAGE: 6VDC
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2011/65/EC (ROHS) COMPLIANT



E-SWITCH®

A	22526	New Release	9/28/16	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE R713FE3-SXXX1B4RAW

SCALE 1:1

DATE 9/28/2016

DR MW

DWG C700034

REV A