




MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



SPECIFICATIONS

TUSONIX PART NO.		848-040-X5U0-472 M
D (Diameter):		.660 +.030, -.050 [16.76 +0.76,-1.27]
T (Thickness):		.120 ± .040 [3.05 ±1.02]
S (Lead Wire Spacing):		.375 ±.060 [9.52 ±1.52]
L (Lead Wire Length):		1.25 [31.75] MIN.
E (Lead Wire Diameter):		.032 [0.81] (20 AWG.)
P (Coating on Leads Max.):		.125 [3.18]
Capacitance Value:		4700 pF
Capacitance Tolerance:		± 20%
Temperature Coefficient:		X5U
Voltage:	Working:	1000 VDC
	Test:	2500 VDC
	Life:	2000 VDC

NOTE:
MIL - P/N CK63AW472M

Marking: TMK, MIL PART NO., DATE CODE.

REVISION RECORD	Original Release C.O. 20060104-6-01	0		--TOLERANCES-- Unless Otherwise Specified	Title	
				DECIMAL ± 	DISC	
				ANGLES ± 		
				TUSONIX TUCSON, ARIZONA		Drawn
			Approved	T.C. 01-04-06		
			A	848-040-X5U0-472M		