







P.C.B. LAYOUT
Top view



N=NUMBER OF POLES

Dim L	(N-1)×10.0+6.0
Dim B	(N-1)×10.0

	Dim L	Dim B
2-4p	±0.25	±0.15
5-8p	±0.35	±0.25
9-12p	±0.45	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	01/24'07	The Soldering temperature from 245° to 250°	Aaron
△	01/24'07	Add "VDE" stipulation	Aaron
△	01/02'13	change the electrical specification and the dimension from 3.6 to 3.3	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUAL Y!!!			

Material

- Item ① Contact pin : Brass.Tin plated
- Item ② Wire guard: Stainless steel
- Item ③ Insulator body: Thermoplastic (UL94V-0)
- Item ④ Insulator lever: Thermoplastic (UL94V-0) Natural color
- Item ⑤ Pad board: Thermoplastic (UL94V-0)
- Item ⑥ Insulating cover :Thermoplastic (UL94V-0)

Electrical cULus VDE △

- Voltage rating: 300VAC 450VAC
- Current rating: 10A 6A
- Wire range: 0.5mm²
- Solid wire(AWG): 14-20
- Stranded wire(AWG): 14-20
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV 2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus VDE
- Critical dimension: △

HBxx11x0xxxxG

No. OF POLES
02: 2 POLES
03: 3 POLES
:
:
12: 12 POLES

- Body Color
- 0 Black (RAL9005)
 - 2 Red (RAL3001/D)
 - 3 Orange(RAL2011/P)
 - 4 Yellow(RAL1018/A)
 - 5 Green(RAL6018/T)
 - 6 Blue (RAL5015/A)
 - 8 Grey(RAL7004/P)
 - 9 White(RAL1102)
 - C Multiple colors

RoHs compliant
(lead<4%)
In copper Alloy

000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HB - 10.0mm Series (Single wire)						
PART NO.	HBxx11x0xxxxG			DWG NO.	8HB0201			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Da cheng 2013.01.02	Da cheng 2013.01.02		UNIT: mm	X.	±0.50	
					SCALE: NONE	X.X	±0.30	
					REV.: F	X.XX	±0.10	
					SHEET: 01/01		X°	±1°