

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

PHYSICAL PROPERTIES:

HOUSING: THERMOPLASTIC, UL94V-0, BLACK.

SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.

PITCH (TERMINAL SPACING): .375"

OPERATING TEMP.: 105° C MAX

ELECTRICAL PROPERTIES:





RATED CURRENT: 20A

OPERATING VOLTAGE: 300V

WIRE RANGE: 12-22 AWG




SEE FIGURE.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

MOUNTING PANEL LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .010
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

DWN 8/2/05

S SCHLEGEL

CHK 8/2/05

S YODER

APVD 8/2/05

S YODER

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	UPDATING STATUS OF 2-1776584-6 FROM PRELIMINARY TO ACTIVE	03DEC2015	FP	PS

2	OBSOLETE	9.436	25	JC6-F408-25	2-1776584-5
1		9.061	24	JC6-F408-24-256	2-1776584-6
		9.061	24	JC6-F408-24	2-1776584-4
		8.686	23	JC6-F408-23	2-1776584-3
		8.311	22	JC6-F408-22	2-1776584-2
		7.936	21	JC6-F408-21	2-1776584-1
		7.561	20	JC6-F408-20	2-1776584-0
		7.186	19	JC6-F408-19	1-1776584-9
		6.811	18	JC6-F408-18	1-1776584-8
		6.436	17	JC6-F408-17	1-1776584-7
		6.061	16	JC6-F408-16	1-1776584-6
		5.686	15	JC6-F408-15	1-1776584-5
		5.311	14	JC6-F408-14	1-1776584-4
		4.936	13	JC6-F408-13	1-1776584-3
		4.561	12	JC6-F408-12	1-1776584-2
		4.186	11	JC6-F408-11	1-1776584-1
		3.811	10	JC6-F408-10	1-1776584-0
		3.436	9	JC6-F408-09	1-1776584-9
		3.061	8	JC6-F408-08	1776584-8
2	OBSOLETE	2.686	7	JC6-F408-07	1-1776584-7
		2.311	6	JC6-F408-06	1776584-6
		1.936	5	JC6-F408-05	1-1776584-5
		1.561	4	JC6-F408-04	1-1776584-4
		1.186	3	JC6-F408-03	1-1776584-3
		.811	2	JC6-F408-02	1-1776584-2
		DIM A	NO OF POS	CATALOG NUMBER	PART NUMBER



TE Connectivity

NAME

JC6-F408-XX ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1776584

SCALE 1:1

SHEET 1 OF 2

REV C2


4

3


2

1

LOC	DIST 0	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—



2-1776584-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 8/2/05	 TE Connectivity				
		CHK S YODER 8/2/05					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .010 4 PLC ± - ANGLES ± -	APVD S YODER 8/2/05	NAME JC6-F408-XX ASSEMBLY				
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		WEIGHT —					
		MATERIAL —	FINISH —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1776584	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 of 2	REV C2		