



This drawing is the property of
Tucsonix, Inc., and may not be
used, reproduced, published or
disclosed to others without ex-
pressed authorization by Tucsonix Inc.


Electrical Testing per Tucsonix standard test plans and Mil-Std-202 Test Methods.

MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTE:
LEAD ORIENTATION
TO HEX NUT REQ'D.



SPECIFICATIONS

TUSONIX PART NO.	2432-032-X5U0-402M
Capacitance:	4000 pF
Tolerance:	± 20 %
Temp. Coefficient:	X5U
Operating Temp.:	-55°C TO 85°C
Working Voltage:	2000 VDC
To Tusonix Spec Unless Stated Otherwise	

NOTES:

1. TUSONIX STANDARD PART NUMBER:
2432-032-X5U0-402M.
TUSONIX RoHS COMPLIANT PART
NUMBER: 2432-032-X5U0-402M LF.
CUSTOMER MUST SPECIFY STANDARD
OR RoHS PART NUMBER WHEN ORDERING.
2. MATERIALS: SILVER PLATED BUSHING, LEAD, AND
MOUNTING HARDWARE.
3. PART MARKING: 3 DOT COLOR CODE; STANDARD
PART: COLORS PER VARIATION.
RoHS PART: 3 DOT COLOR CODE PER VARIATION
PLUS ADDITIONAL GREEN INK DOT OPPOSITE ON
TOP OF HEX.
4. SUPPLIED WITH HEX NUT AND LOCK WASHER.
5. MAXIMUM RECOMMENDED MOUNTING
TORQUE, 9.0 lb-in [1.02 Nm]