





RECOMMENDED PANEL MOUNTING






CIRCUIT: DPDT

SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
		
DN	DIFF	DN
2-3,5-6	OPEN	2-1,5-4

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
3. TERM. NDS. FOR REF. ONLY
4. RATING: 5A @120VAC OR 28VDC;
2A @250VAC
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy w/Silver Plate.
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @50 level
9. OPERATING TEMP.: -30°C to 85°C



b. DIELECTRIC STRENGTH: 100KV RMS @50Hz level 9. OPERATING TEMP.: -30°C to 85°C				
A	12466	RELEASED FOR PRODUCTION	10/7/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

E-SWITCH®				
TITLE				
100 DP-3 T6 B11 VS5 Q E				
SCALE	DATE	DR	DWG	REV
2:1	10/7/02	CJB	T123060	A