





TAPE & REEL	WITHOUT	2357798-4
TAPE & REEL	WITH	2357798-3
HARD TRAY	WITH	2357798-2
HARD TRAY	WITHOUT	2357798-1
PACKAGE	CAP	P/N



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24JUN2019 ART LIN		 TE Connectivity					
		CHK HOPE LU 10OCT2019							
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE					
mm		APVD HOPE LU 10OCT2019							
		PRODUCT SPEC							
		108-32658							
		APPLICATION SPEC							
		114-115003							
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
-		-		A200779	G=2357798		-		
SEE NOTE 1		SEE NOTE 2		CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 6	REV A

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





REFERENCE P.C. BOARD LAYOUT
G: GROUND


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	TE Connectivity		
DIMENSIONS: mm		CHK HOPE LU 10OCT2019			
		APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		
		PRODUCT SPEC 108-32658			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3°		APPLICATION SPEC 114-115003	SIZE A200779 CAGE CODE C-2357798 DRAWING NO RESTRICTED TO -		
MATERIAL - SEE NOTE 1		FINISH - SEE NOTE 2			
CUSTOMER DRAWING			SCALE 2:1	SHEET 2 OF 6	REV A

WITHOUT PICK UP CAP
2357798-1


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



SECT. D-D
(SCALE 2:1)
(CONNECTOR NOT SECTION)



DETAIL C
(SCALE 2:1)





SECT. E-E
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	TE Connectivity		
DIMENSIONS: mm		CHK HOPE LU 10OCT2019			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		
0 PLC ±1 1 PLC ±0.3 2 PLC ±0.15 3 PLC ±0.050 4 PLC ±0.0250 ANGLES ±3°		PRODUCT SPEC 108-32658			
MATERIAL -		APPLICATION SPEC 114-115003	SIZE A200779 CAGE CODE C-2357798 DRAWING NO RESTRICTED TO -		
FINISH -		WEIGHT -			
SEE NOTE 1		SEE NOTE 2	CUSTOMER DRAWING		
			SCALE 2:1	SHEET 3 OF 6	REV A


WITH PICK UP CAP
2357798-2

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




SECT. C-C
(SCALE 2:1)



DETAIL E
(SCALE 4:1)



SECT. D-D
(SCALE 2:1)






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	 TE Connectivity				
		CHK HOPE LU 10OCT2019					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE				
		APVD HOPE LU 10OCT2019					
		PRODUCT SPEC 108-32658	SIZE A200779 DRAWING NO C-2357798 RESTRICTED TO -				
		APPLICATION SPEC 114-115003					
		WEIGHT -					
		MATERIAL -					
		FINISH -					
SEE NOTE 1		SEE NOTE 2	CUSTOMER DRAWING				
			SCALE 2:1		SHEET 4 OF 6		REV A

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


DIRECTION OFF TOP OF REEL

REEL WITH PICK UP CAP
2357798-3


POS. NO. 1




DETAIL F
(SCALE 4:1)



SEE DETAIL F



WEEDING THE COVER TAPE
AROUND THE OUTER
PERIPHERY IN
A TURN.
165°~180° PEELING ANGLE








CONNECTOR DETAIL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN 24JUN2019	TE Connectivity		
DIMENSIONS:		CHK HOPE LU 10OCT2019			
mm		APVD HOPE LU 10OCT2019	NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-32658			
0 PLC ±1		APPLICATION SPEC 114-115003	SIZE A200779		
1 PLC ±0.3		WEIGHT -			
2 PLC ±0.15		CUSTOMER DRAWING	DRAWING NO C-2357798		
3 PLC ±0.050		SCALE 2:1			
4 PLC ±0.0250		SHEET 5 OF 6			
ANGLES ±3°		REV A			
FINISH -					
MATERIAL -					
SEE NOTE 1					
SEE NOTE 2					

REEL WITHOUT PICK UP CAP
2357798-4

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ART LIN CHK HOPE LU APVD HOPE LU PRODUCT SPEC	24JUN2019 10OCT2019 10OCT2019	TE Connectivity	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 1 PLC ± 0.3 2 PLC ± 0.15 3 PLC ± 0.050 4 PLC ± 0.0250 ANGLES $\pm 3^\circ$	APPLICATION SPEC 114-115003	WEIGHT -		
MATERIAL - SEE NOTE 1	FINISH - SEE NOTE 2	CUSTOMER DRAWING	SCALE 2:1	SHEET 6 OF 6	REV A
		NAME 8H PLUG ASSY 220POS FH 0.5MM BTB 16Gbps WITH G-PLATE		SIZE A200779	DRAWING NO C-2357798