


DO NOT
SCALE FROM
THIS PRINT



FSI-1XX-XX-XXX-D-X-XX-XX

NO OF POSITIONS
THREADED: -10, -20, -25, -30, -40, -50
NON-THREADED: -05 THRU -50
[IN MULTIPLES OF 5]

BODY HEIGHT
-06: 6mm (USE C-133-02-XXX)
-10: 10mm (USE C-133-03-XXX)

PLATING
-L: .000010 GOLD ON CONTACT AREA,
.000100-.000250 TIN ON TAIL (USE C-133-XX-L)
-S: .000030 GOLD ON CONTACT AREA,
.000100-.000250 TIN ON TAIL (USE C-133-XX-S)
-STL: .000030 GOLD ON CONTACT AREA,
.000200 TIN LEAD ON TAIL (USE C-133-XX-STL)
-LTL: .000010 GOLD ON CONTACT AREA,
.000200 TIN LEAD ON TAIL (USE C-133-XX-LTL)
-LM: .000010 GOLD ON CONTACT AREA,
.000100-.000250 MATTE TIN ON TAIL (USE C-133-XX-L)
-SM: .000030 GOLD ON CONTACT AREA,
.000100-.000250 MATTE TIN ON TAIL (USE C-133-XX-S)

ROW SPECIFICATION
-D: DOUBLE ROW
(FOR -06 BODY: USE FSI-XX-06-D-XX-X)
(FOR -10 BODY: USE FSI-XX-10-D-XX-X)

OPTION
-TR: TAPE & REEL PACKAGING
BLANK FOR TUBED PARTS.
-P: (FOR AVAILABILITY, SEE FIG 4, SHEET 3)
-K: POLYAMIDE FILM PAD
(USE K-500-300)(SEE FIG 5, SHEET 3)
[AVAILABLE ONLY ON POSITIONS
40 & 50 WITH ANY THREADED
INSERT OPTIONS]

ALIGNMENT PIN LOCATION
-AT: TOP SIDE (USE FSI-XX-XX-D-AT-X)
-AB: BOTTOM SIDE (USE FSI-XX-XX-D-AB-X)
-AD: DUAL (TOP & BOTTOM)
(USE FSI-XX-XX-D-AD-X, SEE FIG 2)
*LC: LOCKING CLIP
BLANK FOR NO ALIGNMENT PIN.

THREADED INSERT OPTION
-E: THREADED INSERT (ENGLISH)
(USE INS-19-2-56-157, SEE FIG 3, SHT 2)
-M: THREADED INSERT (METRIC)
(USE INS-19-M2-157-N, SEE FIG 3, SHT 2)
BLANK FOR NON-THREADED INSERT.

* = NOT TOOLED





TABLE 1			
BODY HEIGHT	"B"	"C"	"D"
-06	.236 [6.00]	.450 [11.43]	.158 [4.01]
-10	.394 [10.00]	.450 [11.43]	.307 [7.80]



TABLE 2	
No. OF POS.	COPLANARITY
0-35	.004 [.10]
40-50	.006 [.15]

.050[1.27] REF .013[0.32] REF




DETAIL 'C'
SCALE 5.5 : 1


- NOTES:
- REPRESENTS A CRITICAL DIMENSION.
 - MINIMUM PUSHOUT FORCE: 12 oz.
 - LOAD INSERTS IN THE DIRECTION OF THE ARROW USING THERMAL INSERTION MACHINE.
 - THREADED INSERT MUST BE ABLE TO HANDLE 35 in.-oz's OF TORQUE MIN WITHOUT ROTATING OR "LOOSENING".
 - THREADED INSERT RETENTION TO BE 20 lb MIN.
 - FOR -05 POS WITH -PPP OPTION, LEADS MAY NOT BE VISIBLE BY SOME OPTICAL MACHINES.
 - HOT BAR FORM AFTER ASSEMBLY (WILL PRODUCE RETENTION FLANGE AS SHOWN).
 - MAXIMUM ALLOWABLE SHEAR BURR: .003[.08], IN DIRECTION SHOWN.



IN-PROCESS 1
[SHOWN WITH CARRIER]



IN-PROCESS 2
[SHOWN WITH CARRIER]



UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [.25]
.XXX: ±.005 [.13]
.XXXX: ±.0020 [.05]



MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1
INSULATOR: LCP, COLOR: BLACK
CONTACTS: C-133-02-X: BeCu
C-133-03-X: BeCu
INSERT: BRASS

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.




520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
1mm SINGLE ELEMENT INTERFACE
DWG. NO.
FSI-1XX-XX-XXX-D-X-XX-XX
BY: BRATCHER 1/29/99 SHEET 1 OF 3



FOR -40- & -50 WITH -M OR -E OPTION
(FSI-150-06-L-D-M-AD SHOWN)



ALIGNMENT PIN OPTION
FOR -40- & -50 WITH -M OR -E OPTION
(FSI-150-XX-L-D-M-AD SHOWN)

FIG 3

-M & -E: THREADED OPTIONS
(FSI-110-06-L-D-M SHOWN)
(EQUATIONS APPLY TO -10, -20, -25 & -30 ONLY)







TABLE 3: THREADED INSERT		
OPTION	INSERT	THREAD
-E	INS-19-2-56-157	2 X 56
-M	INS-19-M2-157-N	M2.0 x 4

**** METRIC THREADED INSERTS TO BE FLASH NICKEL PLATED**

FIG 2
ALIGNMENT PIN OPTIONS
(FSI-110-06-L-D-AD SHOWN)



PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
1mm SINGLE ELEMENT INTERFACE


DWG. NO.
FSI-1XX-XX-XXX-D-X-XX-XX

BY: BRATCHER 1/29/99 SHEET 2 OF 3

FIG 4


**-P: PICK & PLACE PAD OPTION
(FSI-110-06-L-D-M SHOWN)
NOT AVAILABLE ON 5 POSITION**

NOT AVAILABLE IF POSITION IS 05 AND LEAD STYLE IS 06



FOR 10 THRU 50 POSITIONS WITH -M OR -E OPTION,
-10 THRU -50 WITHOUT -M OR -E OPTION

BODY HEIGHT	"E"	"F"
-06	.306 [7.77]	.241 [6.12]
-10	.464 [11.79]	.399 [10.13]

$$\begin{aligned} \text{"M"} &= (\text{No OF POS} \times .03937[1.000]) + .030[.76] \text{ REF} \\ \text{"P"} &= \{(\text{"M"} - .200[5.08]) / 2\} \pm .020[.51] \end{aligned}$$


PACKAGING TABLE

PACKAGING TABLE		
BODY HEIGHT	TUBE	PLUG
-06	PT-1-24-02-70	TP-29
-10	PT-1-24-02-106	TP-13
-06-P	PT-1-24-03-101	TP-03
-10-P	PT-1-24-04-101	TP-13





FIG 5

-K: POLYAMIDE FILM PAD
(USE K-500-300)
(AVAILABLE ONLY ON POSITIONS
40 & 50 WITH -M OR -E OPTION)

$$\begin{aligned} \text{"T"} &= (\text{No OF POS} \times .03937[1.000]) + .870[22.10] \text{ REF} \\ \text{"U"} &= \{(\text{"T"} - .315[8.00]) / 2\} \pm .020[.51] \end{aligned}$$

* **PROPRIETARY NOTE**
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOT REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

santec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION: 1mm SINGLE ELEMENT INTERFACE

DWG. NO.
FSI-1XX-XX-XXX-D-X-XX-XX

BY: BRATCHER 1/29/99

SHEET 3 OF 3