








PANEL CUTOUT

SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
1-2	OPEN



NOTE:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- CONTACT RATING: 20A 125VAC T65 [UL, cUL]
12A 250VAC T65 [UL, cUL]
10(4)A 250V~ 5E4 T125/55 [ENEC10, VDE]
- CONTACT RESISTANCE: 35mΩ MAX. @ 50VAC
- INSULATION RESISTANCE: 100MΩ MIN. @ 500VAC
- DIELECTRIC STRENGTH: 1,500VAC FOR 1 MINUTE
- ELECTRICAL LIFE: 6,000 CYCLES [UR, cUR]
50,000 CYCLES [ENEC10, VDE: 10(4)A 250V~]
- OPERATING TEMPERATURE: -20°C TO 65°C [UR, cUR]
-20°C TO 125°C [ENEC10, VDE: 10(4)A 250V~]
- ▲ DENOTES CRITICAL PARAMETER
- 2002/95/EC (ROHS) COMPLIANT



TITLE RR551D1921

A	21772	RELEASE FOR PRODUCTION	1/23/15	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1	DATE 1/23/2015	DR rc	DWG 14-RR551D1921	REV A
--------------	-------------------	----------	----------------------	----------