


RECOMMENDED PANEL MOUNTING


PANEL THICKNESS

1.52 TO 3.18

* DIMENSION IS 15.75/15.88
FOR PANEL THICKNESS BETWEEN
1.52mm TO 3.18mm



BOTTOM VIEW



CIRCUIT: 4PDT
CONTACT CONFIGURATION

SWITCH FUNCTION			
POS. 1	POS. 2	POS. 3	
DN	NONE	DN	
2-3, 5-6	DPEN	2-1, 5-4	
8-9, 11-12		8-7, 11-10	

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 2 AMPS @ 250VAC
5 AMPS @ 120VAC OR 28VDC
5. CONTACT RESISTANCE: 10mILLI Ohms max initial
@2-4VDC, 100mA for AG & AU
6. ELECTRICAL LIFE: 50,000 make-and-break
cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to 85°C



CORRECT RATING				TITLE			
D	19948			BMA	300 4P-1 R6 BLK M1 Q E BLK		
C	12202	REVISED AND REDRAWN	5/31/02	CB			
REV.	ECN No.	DESCRIPTION	DATE	CHKD	SCALE	DATE	DR
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					2:1	5/31/02	CB
							DWG
							REV