






ENVIRONMENTAL CHARACTERISTICS	MIN	MAX	UNIT
OPERATING TEMPERATURE	-5	50	°C
RELATIVE HUMIDITY OPERATING, NON-CONDENSING ENVIRONMENT	5	95	%


NOTES:

1. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING,
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS).
3. SEPARATE LENS IS AVAILABLE UNDER TE P/N: 2317697-1.
4. OBSOLETE



	W/MICROPHONE, W/O HEADER	A	1-2314277-2
	W/O MICROPHONE, W/O HEADER	A	1-2314277-1
4	W/MICROPHONE, W/HEADER	A	2314277-2
4	W/O MICROPHONE, W/HEADER	A	2314277-1
	COMMENTS	REV	PART NO.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10MAR2017 J. SHAFFER CHK 10MAR2017 C. GINGRICH		 TE Connectivity			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
mm		0 PLC ±. 1 PLC ±0.4 2 PLC ±0.25 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		AMBIMATE, MSM4 SENSOR MODULE, THRU HOLE - PIN HEADER			
				PRODUCT SPEC		DRAWING NO	
				108-133092		RESTRICTED TO	
				APPLICATION SPEC			
				114-133092			
MATERIAL				WEIGHT			
-		-		-		-	
-		-		-		-	
CUSTOMER DRAWING						SCALE	REV
						3:1	B1



© 2021 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 10MAR2017	 TE Connectivity			
DIMENSIONS:		CHK C. GINGRICH 10MAR2017				
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD -	NAME AMBIMATE, MSM4 SENSOR MODULE, THRU HOLE - PIN HEADER			
	0 PLC ± 1 PLC ±0.4 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± FINISH	PRODUCT SPEC 108-133092 APPLICATION SPEC 114-133092 WEIGHT -				
MATERIAL -	-	CUSTOMER DRAWING	SIZE A2	CAGE CODE -	DRAWING NO C-2314277	RESTRICTED TO -
-	-		SCALE 3:1	SHEET 2	OF 2	REV B1