

Frequency Mixer WIDE BAND

Level 13 (LO Power +13 dBm) 7300 to 20000 MHz

SIM-24MH+



Generic photo used for illustration purposes only

CASE STYLE: HV1195


Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
For extended temperature range, consult factory.	
Permanent damage may occur if any of these limits are exceeded.	


Pin Connections

LO	8
RF	4
IF	2
GROUND	1,3,5,6,7

Outline Drawing



PCB Metal Land Pattern




Suggested Layout, Tolerance to be within .002

Outline Dimensions (inch)

A	B	C	D	E	F	G
.200	.180	.087	.025	.050	.028	.043
5.08	4.57	2.2098	0.64	1.27	0.71	1.09
H	J	K	L	M	N	wt
.050	.030	.043	.204	.127	0.065	grams
1.27	0.76	1.09	5.18	3.23	1.65	0.08

Demo Board MCL P/N: TB-458+ Suggested PCB Layout (PL-284)



- NOTES:
- TRACE WIDTH AND GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .0028±.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
 - BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
 - COPLANAR WAVEGUIDE: .038 LINE WIDTH & .015 GAP, 3 PL. (SEE NOTE BELOW)
 - PACKAGE OUTLINE
 - PIN 1
 - #.013 PTH FOR GROUND
 - DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).
 - DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

Features

- wide bandwidth, 7300 to 20000 MHz
- low conversion loss, 5.7 dB typ.
- high L-R isolation, 36 dB typ.
- excellent IF BW, DC to 7500 MHz
- LTCC double balanced mixer
- tiny size, low profile, 0.08"
- useable as up and down converter
- aqueous washable
- protected under U.S. Patent 7,027,795

Applications

- fixed satellite
- mobile
- radio location

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS* (dB)			LO-RF ISOLATION (dB)		LO-IF ISOLATION (dB)		IP3 at center band (dBm)
LO/RF $f_L - f_U$	IF	Typ.	σ	Max.	Typ.	Min.	Typ.	Min.	Typ.
7300-20000	DC-7500								
7300-10000		7.0	0.2	8.5	43	31	19	13	20
10000-14500		5.7	0.1	7.5	36	29	18	13	16
14500-18000		7.6	0.3	9.3	26	19	15	10	18
18000-20000		8.5	0.3	10.9	28	22	25	16	25


1 dB COMPR. +9 dBm typ.

* Conversion loss at 30 MHz IF. σ is a measure of repeatability from unit to unit.

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm	LO +13dBm
7300.00	7330.10	6.65	43.77	18.89	3.94	6.09
7500.00	7530.10	6.32	39.57	19.63	3.47	8.37
8000.00	8030.10	6.12	35.84	20.35	2.76	4.99
9000.00	9030.10	7.38	48.14	19.20	4.81	2.76
9500.00	9530.10	7.00	48.23	17.30	3.84	2.56
10000.00	10030.10	6.73	45.78	16.83	3.38	2.62
10500.00	10530.10	6.29	42.22	17.92	3.17	3.22
11000.00	11030.10	5.93	40.36	19.17	2.35	2.25
12000.00	12030.10	5.84	35.97	18.67	1.99	3.49
12500.00	12530.10	5.55	34.02	18.08	1.92	2.31
13000.00	13030.10	5.70	33.28	18.18	1.48	2.28
14000.00	14030.10	5.74	34.81	19.35	1.87	2.77
14500.00	14530.10	6.21	36.04	21.54	2.52	3.07
15000.00	15030.10	6.80	35.11	28.80	2.98	4.28
15500.00	15530.10	6.92	31.74	22.63	2.49	3.20
16000.00	16030.10	7.08	27.52	16.03	2.47	2.97
17000.00	17030.10	7.94	26.56	15.86	4.43	1.25
18000.00	18030.10	8.16	29.19	24.93	2.49	1.99
19000.00	19030.10	7.75	31.50	28.10	3.12	2.04
20000.00	20030.10	9.60	26.59	22.49	2.54	1.27

Electrical Schematic











Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp


www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

 REV. C
 ECO-000060
 SIM-24MH+
 ED-13229/1
 DJ/CP/AM
 200821



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp

