




O.P. (MM)	P.T. (MM)
9.5 ±1.3	5.4 MAX

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.XX=± 0.4
X.XX=± 0.25
3. RATING: 5A @125/250VAC UL, CUL APPROVED
- ▲4. OPERATING FORCE: 10± 6 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. PACKAGE: TRAY, 270 PIECES PER TRAY.

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100798	REMOVE VDE RATING AND LOGO	03/23/22	JS	TITLE MS0850503F010C1A				000021282
					SCALE	DATE	DR	DWG	REV
					2:1	12/16/2014	TN	Q970147	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED