








REAL CODED

|   | C | 1 | 2 | 4 | 8 |
|---|---|---|---|---|---|
| 0 | ● |   |   |   |   |
| 1 | ● | ● |   |   |   |
| 2 | ● |   | ● |   |   |
| 3 | ● | ● | ● |   |   |
| 4 | ● |   |   | ● |   |
| 5 | ● | ● |   | ● |   |

## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REFERENCE ONLY
4. OPERATING TORQUE: 700gf MAX.
5. CONTACT RATING: 150mA, 42V DC (SWITCHING)  
200mA, 42V DC (NON-SWITCHING)
6. CONTACT RESISTANCE: 80m $\Omega$  MAX.
7. INSULATION RESISTANCE: 100M $\Omega$  MIN @ 250VDC
8. DIELECTRIC STRENGTH: 250VAC 1 MIN.
9. LIFE: 10,000 STEPS
10. OPERATING TEMPERATURE: -40°C to 85°C
- ▲ 11. PACKAGING: 50 PCS TUBE
12. IP RATING: IP67
13. ▲ DENOTES CRITICAL PARAMETER



|     |        |                        |         |    |
|-----|--------|------------------------|---------|----|
| A   | 23921  | Release for Production | 6/17/19 | MW |
| REV | PCR NO | DESCRIPTION            | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE RDTDR06R2T

SCALE 2:1

DATE 6/17/2019

DR MW

DWG U200051

REV A